





Result:	550	(576.2) ^{QF}				
Series:	89	94	94	88	95	90
Shot value:	23	27	7	3	0	0
Inner ten:	6					
Furthest:	2479 (39), 2467 (57), 2431 (12)					
Best divider	147.4 (2.) 180.6 (56.) 277.3 (46.)					
Shot position	1.71 mm Left, 0.66 mm Low					
Dispersion value	8.57, Horizontal: 8.52, Vertical: 8.62					




Series 1:	10.5 *	10.8 *	9.5 ↙	9.0 ↘	8.7 ↗
	8.6 ↗	9.3 ↘	9.9 ←	8.8 ↑	9.0 ↙
Best divider	147.4 (2.) 327.5 (1.) 870.5 (8.)				
Shot position	2.10 mm Left, 3.43 mm High				
Dispersion value	9.65, Horizontal: 8.41, Vertical: 10.75				




Series 2:	10.3 ↓	7.9 ←	10.2 ←	10.4 ↘	10.0 ↙
	9.5 ↓	9.2 ↗	9.2 ↓	10.0 ↘	10.3 ↘
Best divider	480.8 (14.) 527.2 (11.) 542.3 (20.)				
Shot position	2.31 mm Left, 2.85 mm Low				
Dispersion value	8.23, Horizontal: 9.33, Vertical: 6.97				




Series 3:	9.3 ↓	8.9 ↘	9.2 ←	9.3 ↘	10.2 ↑
	10.2 ↓	10.5 *	10.0 ↗	9.6 ↙	10.2 ↘
Best divider	349.8 (27.) 604.2 (25.) 621.0 (26.)				
Shot position	0.56 mm Left, 2.90 mm Low				
Dispersion value	7.57, Horizontal: 7.80, Vertical: 7.34				



Series 4:	10.2 ↓	8.7 ↘	9.8 ↘	9.0 ↑	9.3 ←
	9.7 ↙	8.9 ←	10.1 ↙	7.9 ↓	9.4 ↘
Best divider	626.1 (31.) 695.2 (38.) 932.7 (33.)				
Shot position	4.64 mm Left, 2.80 mm Low				
Dispersion value	9.90, Horizontal: 8.45, Vertical: 11.16				



Series 5:	10.0 →	10.2 ↓	9.8 ↘	10.2 ↗	9.8 ↘
	10.6 *	10.1 ↘	10.2 ↗	9.1 ↓	8.6 ↙
Best divider	277.3 (46.) 579.2 (44.) 623.4 (42.)				
Shot position	2.39 mm Left, 1.54 mm Low				
Dispersion value	7.10, Horizontal: 6.06, Vertical: 8.01				



Series 6:	9.6 ↗	9.9 ↗	9.9 →	9.1 ↗	10.5 *
	10.7 *	7.9 ↘	9.6 →	9.7 →	9.2 ←
Best divider	180.6 (56.) 373.1 (55.) 859.6 (52.)				
Shot position	1.72 mm Right, 2.69 mm High				
Dispersion value	8.86, Horizontal: 11.15, Vertical: 5.71				

Meyton Elektronik

ISSF AP Women Jun – *Competition* –

Firing point no: 29

Frejd, Izabella #288

StartNr: 140

27. November 2021 10:51

Öckerö SF

QF – Qualified for Finals

signature of shooter

Meyton Elektronik